

COMPATIBILITY

The Mektronic transmission system is compatible with only HG and ED 9 speed (see page 72).

This compatibility allows immediate use on many bikes without any modifications.

However, we offer you a solution for each case that you could experience using the chart below that stipulates which cassette (and which spacer kit, if necessary) you should install according to the wheel that is currently used.

TYPE OF WHEEL	Mavic		Shimano		Campagnolo	
	HG	CC9	HG		ED	
			8 speed	9 speed	8 speed	9 speed
CASSETTE	Shimano HG 9 speed	Mavic CC9* or M9*	Shimano HG 9 speed		Marchisio or TA 9 speed	Campagnolo ED 9 speed

* use the Mavic kit CC9-M9 reference M40409

In 1999, Mavic will market the M9 cassette.

This is a cassette CC9 (9 cogs + yellow spacers) with the Mavic kit CC9-M9.

This kit (reference M40409) consists of :

- 6 gray spacers (thickness 2.85 mm).
- 2 gray spacers for the 21 and 22 cogs (thickness 2.85 mm).
- 2 gray spacers for the 23 - 27 cogs (thickness 2.85 mm).
- 1 white wedge M40417 (thickness : 1.8mm)

This kit M40409 must be used to obtain perfect compatibility with the Mektronic transmission system.

Therefore, if your customer uses a MAVIC CC9 wheel, two possibilities are offered :

Mavic CC9 wheel + Mavic CC9 cassette + Mavic CC9-M9 Kit
or
Mavic CC9 wheel + Mavic M9 cassette

In both cases, please use the following instructions :

- 1 If necessary, remove the yellow spacers.
- 2 First, put the white wedge M40417 on the body of the free wheel.
- 3 Alternately put on one cog, then a gray spacer until the starting cog.
- 4 Tighten the cassette fixing nut
Torque : 40 N.m. / 350 In.LBS.

